



## GENERAL SEMISOLIDO/VERTICALE M3

### Line

POLYESTER

---

### Function

FOR SLAB PLASTER-WORK IN AUTOMATIC AND NO

---

### Materials

TRAVERTINE

---

### How to use

For best results mix 2% to 3% of the catalyst with the adhesive; the paste formula make easy to measure. A homogeneous mixing will facilitate uniform catalysis. The catalysis rate is effected by temperature and by the proportion/quantity of catalyst. An excess of hardener/catalyst will increase the hardening speed, but weakens the adhesive seal.

---

### Packaging

125ml-500ml-750ml □  
1-4lt □  
19lt

---

### Characteristics

FOR MORE INFORMATIONS ASKING TECHNICAL DATA SHEET

---

### Important

ALWAYS EFFECT A PRELIMINARY TEST BEFORE THE APPLICATION

---